


1104C-44T Industrial Open Power Unit

67-74.5 kW (90-100 hp) @ 2300-2400 rpm

EU Stage II/U.S. EPA Tier 2 equivalent

Whatever your application, there's an 1104 engine for you. Part of the Perkins 1100 Series, the range's 4 cylinder, 4.4 litre engines are smooth and quiet in operation. Designed to meet EU Stage II/IIIA and U.S. EPA Tier 2/Tier 3 equivalent emissions standards, the 1104 range offer a choice of mechanical or electronically controlled common rail engines. Electronically controlled engines deliver the right fuel injection for the load applied to the engine. Common front and rear ends, connection points and components across the range, making it easy to install a different 1100 Series engine in your application.) Turbocharged engines designed to meet EU Stage II/U.S. EPA Tier 2 equivalent emissions standards for off road machines.



Specifications

Power Rating		
Minimum power	67 kW	90 hp
Maximum power	74.5 kW	100 hp
Rated speed	2300-2400 rpm	
Maximum torque	412 Nm @ 1400 rpm	304 lb-ft @ 1400 rpm

Emission Standards	
Emissions	EU Stage II/U.S. EPA Tier 2 equivalent

General		
Number of cylinders	4 inline	
Bore	105 mm	4.1 in
Stroke	127 mm	5 in
Displacement	4.4 litres	269 cubic in
Aspiration	Turbocharged	
Cycle	4 stroke	
Compression ratio	18.3:1	
Combustion system	Direct injection	
Rotation (from flywheel end)	Anti-clockwise	
Cooling system	Liquid	

www.perkins.com

Photographs are for illustrative purposes only and may not reflect final specification.
All information is substantially correct at time of printing and may be altered subsequently.
Final weights and dimensions will depend on completed specification.

SS-10435205-1000002381-004
MSS-IND-1000002381-006.pdf

Produced In England © 2017 Perkins Engines Company Limited

 **Perkins®**

THE HEART OF EVERY GREAT MACHINE

SS Page 1 of 4
Page: M-1 of M-3

1104C-44T Industrial Open Power Unit

67-74.5 kW (90-100 hp) @ 2300-2400 rpm

EU Stage II/U.S. EPA Tier 2 equivalent

Total coolant capacity	15 litres	4 US gal
Total lubricating capacity	8.4 litres	2.2 US gal

Engine Dimensions*		
Length	1272 mm	50 in
Width	613 mm	24.1 in
Height	962 mm	37.9 in
Dry Weight	485 kg	1069 lb

Disclaimer		
*Final dimensions dependent on selected options	0	0

Features and Benefits

Designed for lesser regulated territories

The 1100 Series range of engines have been specifically designed for use in territories with Stage II/IIIA and Tier 2/3 equivalent emissions standards, using the best technologies to ensure a reliable and easy to maintain machine. With a choice of naturally aspirated, turbocharged and turbocharged aftercooled it offers the best combination of power delivery and response.

Ease of maintenance

All of the engines have 500 hour service intervals. And single side service components, for ease of end user servicing.

Easy to upgrade

Common front and rear ends, connection points and components across the range mean that you can easily install a different 1100 Series engine in your application.

Expertise whenever you need it

With our network of distributors, you will find all the advice you need to ensure you get the right engine. By building strong relationships with you, we make sure you have access to the full power of the Perkins brand and expertise. Our fully trained experts deliver total service support 24/7, 365 days of the year. Whether you need technical information, parts identification or ordering, our distribution network is there to make sure your Perkins engine keeps on running at peak performance.

Oil and fuel filtration

The high quality oil and fuel filtration on our 1100 Series range produces an engine that is reliable and durable. Ecoplus fuel filtration is available to boost its clean running qualities and the engine is capable of running on a wide range of global fuels including biodiesel.

www.perkins.com

Photographs are for illustrative purposes only and may not reflect final specification.
All information is substantially correct at time of printing and may be altered subsequently.
Final weights and dimensions will depend on completed specification.

SS-10435205-1000002381-004
MSS-IND-1000002381-006.pdf

Produced In England © 2017 Perkins Engines Company Limited



THE HEART OF EVERY GREAT MACHINE

SS Page 2 of 4
Page: M-2 of M-3

1104C-44T Industrial Open Power Unit

67-74.5 kW (90-100 hp) @ 2300-2400 rpm

EU Stage II/U.S. EPA Tier 2 equivalent

Technical Information

Air Inlet System

- Integral inlet manifold

Control system

- 12 or 24 volt alternator
- 12 or 24 volt starter motor

Cooling system

- Radiator
- Gear driven coolant pump

Flywheels and flywheel housing

- Flywheel housing SAE3

Fuel system

- Ecoplus fuel filter

General

- Balancer or non-balancer
- Cast iron engine block
- Glow plug starting aid
- Pusher or puller fan options

Oil system

- Lub oil sump steel, falt-bottomed with dipstick on left-hand side
- Oil filler - middle of top cover
- Spin-on oil filter

Power take-off

- Left-hand side PTOs - 142 Nm (104.7 lb-ft)

www.perkins.com

Photographs are for illustrative purposes only and may not reflect final specification.
All information is substantially correct at time of printing and may be altered subsequently.
Final weights and dimensions will depend on completed specification.

SS-10435205-1000002381-004
MSS-IND-1000002381-006.pdf

Produced In England © 2017 Perkins Engines Company Limited




THE HEART OF EVERY GREAT MACHINE

SS Page 3 of 4
Page: M-3 of M-3

1100 Series 1104C-44T INDUSTRIAL ENGINE

EU Stage II/U.S. EPA Tier 2 equivalent

72.5-74.5 kW / 97.2-99.9 hp



Power kW	Power hp	Rated Speed (rpm)	Torque Nm	Torque lb-ft	Speed (rpm)	Rating Type
72.5	97.2	2000	408	553	1350	Industrial C intermittent rating
74.0	99.2	2100	408	553	1350	Industrial C intermittent rating
74.5	99.9	2200	408	553	1350	Industrial C intermittent rating
74.5	99.9	2300	408	553	1350	Industrial C intermittent rating

Rating Standard ISO 14396:2002

Additional ratings are available for specific customer requirements. Consult your Perkins distributor.

Unless otherwise specified, all stated data is for maximum rated speed and 100% load.

B rating performance data will be added upon availability

Rating Definitions and Conditions

IND-C (Intermittent) Rating

Is the horsepower and speed capability of the engine where maximum power and/or speed are cyclic (time at full load not to exceed 50%).

Rating Conditions for Diesel Engines – up to 7.1 liters are based on ISO/TR14396, inlet air standard conditions with a total barometric pressure of 100 kPa (29.5 in. Hg), with a vapor pressure of 1 kPa (0.295 in Hg) and 25°C (77°F). Performance is measured using fuel to specification EPA 2D 89.330-96 with a density of 0.845-0.850 kg/L @ 15°C (59°F) and fuel inlet temperature 40°C (104°F).

www.perkins.com

Photographs are for illustrative purposes only and may not reflect final specification.
All information is substantially correct at time of printing and may be altered subsequently.
Final weights and dimensions will depend on completed specification.



THE HEART OF EVERY GREAT MACHINE