# 403D-15T Industrial Diesel Engine

23.1-30 kW (31-40.2 hp) @ 2200-3000 rpm EU Stage IIIA/U.S. EPA Tier 4 Interim equivalent

The Perkins 400 Series is an extensive family of engines in the 0.5-2.2 litre range. The 3 cylinder 403-15 model is the mid-range 400 Series engine, combining performance, low operating costs and a compact package. From a packaging point of view, the 403-15 is the ideal engine for small industrial applications. Its simple, robust mechanical fuel system makes it easy to install and maintain.

A 3 cylinder, turbocharged engine offering increased power with minimal impact on package size.

Designed to meet EU Stage IIIA/U.S. EPA Tier 4 Interim equivalent emission standards.



## **Specifications**

Power Rating				
Minimum power	31 hp			
Maximum power	30 kW	40.2 hp		
Rated speed	2200-3000 rpm			
Maximum torque	111.9 Nm @ 1800 rpm	82.5 lb-ft @ 1800 rpm		

Emission Standards	
Emissions	EU Stage IIIA/U.S. EPA Tier 4 Interim equivalent

General			
Number of cylinders	3 inline		
Bore	84 mm	3.3 in	
Stroke	90 mm	3.5 in	
Displacement	1.5 litres	91 cubic in	
Aspiration	Turbocharged		
Cycle	4 stroke		
Compression ratio	22.5:1		
Combustion system	Indirect injection		
Rotation (from flywheel end)	Anti-clockwise		
Cooling system	Liquid		

# www.perkins.com

Photographs are for illustrative purposes only and may not reflect final specification. All information is substantially correct at time of printing and may be altered subsequently. Final weights and dimensions will depend on completed specification.



# 403D-15T Industrial Diesel Engine

23.1-30 kW (31-40.2 hp) @ 2200-3000 rpm

EU Stage IIIA/U.S. EPA Tier 4 Interim equivalent

Total coolant capacity	2.6 litres	0.7 US gal	
Total lubricating capacity	6 litres	1.6 US gal	

Engine Dimensions*				
Length 572 mm 2				
Width	541 mm	21.3 in		
Height	643 mm	25.3 in		
Dry weight	156.5 kg	345 lb		

Disclaimer		
*Final dimensions dependent on selected options	0	0

#### **Features and Benefits**

#### A lifetime of low cost

The 400 Series offers highly competitive performance and fuel economy. Through appropriate use of technology, these engines have been designed to be reliable and to offer low cost of ownership in the wide variety of markets they serve.

Across an extensive power band, the 400 Series range offers you the ability to configure a solution to your specific machine, territory and market requirements. Overlapping power bands between models and an extensive range of options gives the opportunity to optimise performance and functionality.

We provide one year warranties for constant speed engines and two year warranties for variable speed models as standard.

As a 400 Series end user, you also benefit from Perkins world class product support and service coverage that comes from being a full range power solutions provider.

### Compact design

The compact design of these engines makes them suitable for a range of applications, including skid steer loaders, mini excavators, wheel loaders, welders, lift platforms, lighting towers, small tractors, air compressors, turf care machinery and materials handling machinery.

Each of the six core engines of the 400 Series is configured for either Stage IIIA/Tier 4 Interim or Stage IIIB/Tier 4 Final emission standards, giving you flexibility depending on your market.

#### Performance and refinement

The 400 Series lineup gives you a seamless power range of 8.2-50 kW (11-67 hp) in 2, 3 and 4 cylinder models designed with a family look and feel. The range offers a wide variety of ratings and configurations that can be tailored to meet the most exacting needs.

The selective use of indirect and direct injection fuel systems enables Perkins to offer world-class engine refinement and low noise levels.



**Perkins**®

Photographs are for illustrative purposes only and may not reflect final specification. All information is substantially correct at time of printing and may be altered subsequently. Final weights and dimensions will depend on completed specification.

# 403D-15T Industrial Diesel Engine

23.1-30 kW (31-40.2 hp) @ 2200-3000 rpm EU Stage IIIA/U.S. EPA Tier 4 Interim equivalent

## **Technical Information**

#### Air inlet system

- · Cast iron exhaust manifold side outlet
- · Inlet manifold

### Control system

- 12 and 24 volt alternator
- 12 and 24 volt starter motor
- · Engine shut-off solenoid

## Cooling system

- · Coolant pump belt driven
- · Coolant temperature switch
- · Cooling fan, high and low fan position

#### Flywheel and flywheel housing

#### Fuel system

- CTD Fuel injection pump
- · Spin-on fuel filter

#### General

- · Cast iron engine block
- · Glow plug starting aid
- Cold start capability to -20°C (-4°F) (aided)

### Oil system

- · Lubricating oil pressure switch
- · Lubricating oil sump
- · Spin-on lubricating oil filter

#### Power take-off

SAE A PTO






# 400 Series 403D-15T INDUSTRIAL ENGINE

EU Stage IIIA/U.S. EPA Tier 4 Interim equivalent

23.0-30.0 kW / 30.8-40.2 hp



Power kW	Power hp	Rated Speed (rpm)	Torque Nm	Torque lb-ft	Speed (rpm)	Rating Type
23.0	30.8	2200	112	151	1800	Industrial C intermittent rating
25.0	33.5	2400	112	151	1800	Industrial C intermittent rating
27.5	36.9	2600	112	151	1800	Industrial C intermittent rating
29.5	39.6	2800	112	151	1800	Industrial C intermittent rating
30.0	40.2	3000	112	151	1800	Industrial C intermittent rating

#### Rating Standard ISO 14396:2002

Additional ratings are available for specific customer requirements. Consult your Perkins distributor.

Unless otherwise specified, all stated data is for maximum rated speed and 100% load.

B rating performance data will be added upon availability

#### **Rating Definitions and Conditions**

## IND-C (Intermittent) Rating

Is the horsepower and speed capability of the engine where maximum power and/or speed are cyclic (time at full load not to exceed 50%).

Rating Conditions for Diesel Engines – up to 7.1 liters are based on ISO/TR14396, inlet air standard conditions with a total barometric pressure of 100 kPa (29.5 in. Hg), with a vapor pressure of 1 kPa (0.295 in Hg) and 25°C (77°F). Performance is measured using fuel to specification EPA 2D 89.330-96 with a density of 0.845-0.850 kg/L @ 15°C (59°F) and fuel inlet temperature 40°C (104°F).

# www.perkins.com

Photographs are for illustrative purposes only and may not reflect final specification. All information is substantially correct at time of printing and may be altered subsequently. Final weights and dimensions will depend on completed specification.



THE HEART OF EVERY GREAT MACHINE